


# Product data sheet

Specifications



slot nuts, slot size 8, M8 - 10 pieces

VW33MF010T8N8

## Main

Range Of Product	Lexium linear motion
Product Or Component Type	T-slot nut
Product Specific Application	To mount the axis on fixed support
Accessory / Separate Part Category	Maintenance accessories
Screw Type	M8

## Complementary

Product Compatibility	PAS 44 linear axis 110 x 110 mm TAS 42 linear axis 150 x 54 mm TAS 43 linear axis 200 x 59 mm CAS 44 linear axis 110 x 110 mm
Range Compatibility	Lexium PAS Lexium TAS Lexium CAS
Width	0.31 in (8 mm)

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	5.12 in (13.0 cm)
Package 1 Length	7.48 in (19.0 cm)
Package 1 Weight	6.00 oz (170.0 g)
Unit Type Of Package 2	S04
Number Of Units In Package 2	30
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	14.00 lb(US) (6.352 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product’s sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	

Dimensions Drawings

Dimensions



Dimensions in mm

B	H	L	LA	ØD
13.8	7.3	23	7.5	M8

Dimensions in in.

B	H	L	LA	ØD
0.54	0.29	0.90	0.29	M8