Product data sheet

Specifications





Rotating beacon, 84 mm, blue, without buzzer, 12 V AC DC

XVR08J06

() Discontinued on: Feb 18, 2022

() Discontinued

Main

Range Of Product	Harmony XVR
Product Or Component Type	Prewired rotating mirror beacon
Sound Signalling	Without
Device Short Name	XVR
Mounting Diameter	3.31 in (84 mm)
Ip Degree Of Protection	IP65 IEC 60529 with accessory) IP23 IEC 60529
[Us] Rated Supply Voltage	12 V AC/DC
Light Source	High luminosity LED, blue

Complementary

<u> </u>	
Material	ABS (acrylonitrile butadiene-styrene): body part PC: globe
Cad Overall Width	3.31 in (84 mm)
Cad Overall Depth	3.31 in (84 mm)
Net Weight	0.66 lb(US) (0.3 kg)
Marking	CE
Product Mounting	By 3 M4 screws
Supply Voltage Limits	1015 V DC 10.813.2 V AC
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	250 mA
Flashing Frequency	2.3 Hz
Clamping Connection Capacity	0.83 mm ²
Awg Gauge	AWG 18
Cable Length	19.69 in (500 mm)

Environment

Standards	EN 61000-6-2 EN 61000-6-4
Product Certifications	UL
Protective Treatment	тс

Ambient Air Temperature For Storage	-31158 °F (-3570 °C)
Ambient Air Temperature For Operation	14122 °F (-1050 °C)
Fleetwisel Check Protection Class	

Electrical Shock Protection Class Class II IEC 61140

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	3.74 in (9.5 cm)
Package 1 Length	7.28 in (18.5 cm)
Package 1 Weight	13.76 oz (390 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


Product data sheet

Dimensions Drawings

Rotating Mirror Beacon

Dimensions





Product data sheet

Mounting and Clearance

Rotating Mirror Beacon

Panel Cut-out

