# **Product datasheet**

Specification





# voltage release MX or XF COM - 100..130 V AC/DC

33035

### Main

Range	MasterPacT
Range Of Product	MasterPact NT MasterPact NW
Device Short Name	MX com XF com
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Opening coil Closing coil
Control Type	Communicating
[Uc] Control Circuit Voltage	100130 V AC 50/60 Hz 100130 V DC
Circuit Breaker Mounting Mode	Fixed Drawout
Range Compatibility	Masterpact MasterPact NT Masterpact MasterPact NW

## Complementary

Operating Threshold	0.71.1 x Un opening
Response Time	55 ms +/- 10 % for MasterPact NT 70 ms +/- 10 % for MasterPact NW 50 ms +/- 10 % for Compact NS630b1600 50 ms +/- 10 % for Compact NS1600b3200
Supply Holding Power	4.5 VA
Accessory / Separate Part Category	Spare part for MasterPact NT Spare part for MasterPact NW

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.0 cm
Package 1 Length	8.2 cm
Package 1 Weight	152.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Height	9.0 cm
Package 2 Width	13.0 cm
Package 2 Length	18.5 cm
Package 2 Weight	1.56 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	40
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	6.65 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information