## **Product datasheet**

Specification





# Mureva lights, Floodlight 200W, IP65 230V

IMT47223

### Main

Range	Mureva
Range Of Product	Mureva lights
Product Or Component Type	Floodlight
Device Application	Ware-houses and parking garages Residential Media device support
	Public areas
	Secure lighting
	Stadiums and arenas

## Complementary

Type Of Installation	Outdoor
Total System Power	200 W
Light Source	LED
[Ue] Rated Operational Voltage	230 V AC
Power Factor	0.9
Colour Rendering Index	R <sub>a</sub> =80
Luminous Flux	24000 lm
Bulb Lifespan	50000 h
Colour Temperature	6500 K
Colour Tint	Black
Provided Equipment	Sensor
Electrical Insulation Class	Class E
Beam Angle	110°
Shape	Rectangular
Height	342.0 mm
Width	278.0 mm
Depth	61.0 mm
Net Weight	4.9 kg

### **Environment**

Environmental Characteristic	Weatherproof	
Ip Degree Of Protection	IP65	
Ik Degree Of Protection	IKU6	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For -30...45 °C
Operation

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.6 cm
Package 1 Width	34.2 cm
Package 1 Length	42.4 cm
Package 1 Weight	5.524 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	2
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	12.47 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	16
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	111.76 kg

## **Contractual warranty**

Warranty 5 years



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Sustainable Packaging Transparency RoHS/REACh

#### Resource performance



Sustainable Packaging

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information