Product datasheet

Specification





Actassi - patch cord - category 6 - 24 AWG - UTP - 1 m - grey - CM

ACTPC6UBCM10GY_E

- Discontinued on: Sep 4, 2023
- ! To be end-of-service on: Sep 3, 2025

(!) Discontinued

Main

Range	Actassi
Product	Patch cord
Colour	Grey
Cable Shielding Type	IITP

Complementary

Type Of Cable	4 pair cables	
Rated Voltage	150 V AC	
[In] Rated Current	1.5 A	
Insulation Resistance	500 MOhm	
Length (Customizable Value In Configurator)	01 m	
Communication Network Category	6	
Contacts Material	Phosphor bronze with 50 micro-inches gold over 100 micro-inches nickel	
Contact Resistance	10 mOhm	
Awg Gauge	AWG 24	
Attenuation	Guaranteed: 0.1 dB	
Far End Crosstalk [Fext]	49.8 dB	
Power Sum Far End Crosstalk [Psfext]	46.9 dB	
Minimum Number Of Matings	1000 cycles	
Targeted Region	Asia Pacific.	

Environment

Flame Retardance	СМ
Standards	IEC 60603-7
	FCC part 68 Subpart F
	ISO/IEC 11801 2nd edition
	ANSI/TIA-568-C.2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.02 cm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	21 cm
Package 1 Length	30.2 cm
Package 1 Weight	45.7 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations