Product datasheet

Specifications





Ultra - floor outlet box - 6 modules

ETK44112

- () Discontinued on: Sep 4, 2023
- (!) To be end-of-service on: Sep 3, 2025



Main

Range Of Product	Ultra
Product Or Component Type	Floor outlet box
Type Of Floor	Raised floor In-cavity floor Screeded floor
Floor Box Shape	Rectangular
Product Destination	Wiring device 45 x 45 mm Wiring device 22.5 x 45 mm
Colour Tint	Grey (RAL 7011)
Quantity Per Set	Set of 1

Complementary

Number Of Modules	6 modules
Material	PA (polyamide) 6 GF10
Height	72 mm
Width	269 mm
Depth	187 mm

Environment

Standards	IEC 60670-1 UNE 20451
Ambient Air Temperature For Operation	-560 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.0 cm
Package 1 Width	22.0 cm
Package 1 Length	28.5 cm
Package 1 Weight	1.282 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	5

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.038 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	80.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	121.616 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations