# **Product datasheet**

Specifications





# Mureva lights, Floodlight 50W 6500K, IP65 230V

IMT47213

### Main

Range	Mureva
Range Of Product	Mureva lights
Product Or Component Type	Floodlight
Device Application	Ware-houses and parking garages Residential Media device support Public areas Secure lighting Stadiums and arenas

## Complementary

Type Of Installation	Outdoor
Total System Power	50 W
Light Source	LED
[Ue] Rated Operational Voltage	230 V AC
Power Factor	0.9
Colour Rendering Index	R <sub>a</sub> =80
Luminous Flux	5000 lm
Bulb Lifespan	50000 h
Colour Temperature	6500 K
Colour Tint	Black
Electrical Insulation Class	Class F
Beam Angle	110°
Shape	Rectangular
Height	215.4 mm
Width	161.4 mm
Depth	31.0 mm
Net Weight	1.02 kg

### **Environment**

Environmental Characteristic	Weatherproof
Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK05
Ambient Air Temperature For	-3045 °C

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	17 cm
Package 1 Length	22.5 cm
Package 1 Weight	1.15 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	11.941 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	160
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	203.056 kg

## **Contractual warranty**

Warranty 3 years



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Sustainable Packaging Transparency RoHS/REACh

#### Resource performance



Sustainable Packaging

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information