

# Product datasheet

Specifications



## Unica - HDMI data connector type A - 1 module - graphite

MGU3.430.12

### Main

Range	Unica
Product or component type	Audio/video socket
Connector type	HDMI
Electrical circuit type	Audio/video
Device presentation	Mechanism
Colour tint	Graphite
Type of packing	Group

### Complementary

Device mounting	Flush
Socket number	1
Fixing mode	Clip-in
Number of modules	1 module
Surface finish	Matt
Quantity per set	Set of 10
Material	Thermoplastic ABS-UV stabilised: centre plate
Height	45 mm
Width	22.5 mm
Depth	41.7 mm
Embedding depth	25.7 mm
Net weight	0.01 kg

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...40 °C
Standards	EN 50049 EN 50157
IP degree of protection	IP21
IK degree of protection	IK04

<b>Environmental characteristic</b>	Window-cleaning fluid Alcohol Acetone Liquid soap Petrol Oil Bleach UV resistant
-------------------------------------	---

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Weight</b>	43.0 g
<b>Package 1 Height</b>	2.5 cm
<b>Package 1 width</b>	11 cm
<b>Package 1 Length</b>	12 cm
<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	10
<b>Package 2 Weight</b>	543.0 g
<b>Package 2 Height</b>	8.2 cm
<b>Package 2 width</b>	20 cm
<b>Package 2 Length</b>	22.5 cm
<b>Unit Type of Package 3</b>	S03
<b>Number of Units in Package 3</b>	50
<b>Package 3 Weight</b>	3.18 kg
<b>Package 3 Height</b>	30 cm
<b>Package 3 width</b>	30 cm
<b>Package 3 Length</b>	40 cm

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins