

Product datasheet

Specifications



Unica Top - cover frame - 3 modules - glossy chrome/aluminium

MGU66.103.038

Main

| | |
|---------------------------|---------------|
| Range | Unica |
| Device application | Mounting |
| Product or component type | Cover frame |
| Aesthetic name | Unica Top |
| Number of modules | 3 modules |
| Fixing mode | Clip-in |
| Cover frame colour tint | Glossy chrome |
| Decoration colour | Aluminium |

Complementary

| | |
|----------------|---|
| Material | ASA + PC: intermediate part Zamak: cover frame |
| Standards | EN 60669-1 |
| Height | 116 mm |
| Width | 80 mm |
| Depth | 13.7 mm |
| Net weight | 0.072 kg |
| Market segment | Small commercial Residential |

Environment

| | |
|------------------------------|---|
| IK degree of protection | IK01 |
| IP degree of protection | IP20 |
| Environmental characteristic | Petrol Bleach UV resistant Oil Liquid soap Acetone Window-cleaning fluid Alcohol |

Packing Units

| | |
|------------------------------|-----|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |

| | |
|------------------------------|----------|
| Package 1 Weight | 70.9 g |
| Package 1 Height | 1.5 cm |
| Package 1 width | 8 cm |
| Package 1 Length | 11.6 cm |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 24 |
| Package 2 Weight | 2.687 kg |
| Package 2 Height | 15 cm |
| Package 2 width | 30 cm |
| Package 2 Length | 40 cm |
| Unit Type of Package 3 | BB1 |
| Number of Units in Package 3 | 3 |
| Package 3 Weight | 279.0 g |
| Package 3 Height | 6.5 cm |
| Package 3 width | 12.5 cm |
| Package 3 Length | 18.7 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|