


Product datasheet

Specifications



Switch actuator REG-K/8x230/16 with manual mode, light grey

MTN647893

Main

Range Of Product	KNX
Product Or Component Type	Switch actuator
Operating Mode	Manual
Bus Type	KNX
Modular Device Additional Info	Connectable with different phases
Number Of Contacts	8

Complementary

Total Number Of 18 Mm Modules	8
Mounting Support	DIN rail
[Ue] Rated Operational Voltage	100...240 V
Network Frequency	50...60 Hz
[In] Rated Current	16 A
Load Type	Incandescent lamps: <= 3600 W, 230 V AC Halogen lamps: <= 2500 W, 230 V AC Incandescent lamps: <= 1600 W, 100 V AC Incandescent lamps: <= 3840 W, 240 V AC Halogen lamps: <= 1086 W, 100 V AC Halogen lamps: <= 2608 W, 240 V AC Parallel compensated fluorescent lamp: <= 1086 VA, 100 V AC Parallel compensated fluorescent lamp: <= 2500 VA, 230 V AC Parallel compensated fluorescent lamp: <= 2608 VA, 240 V AC Capacitive: , 16 A, 200 µF, 100...240 V AC

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.300 cm
Package 1 Width	13.000 cm
Package 1 Length	28.000 cm
Package 1 Weight	626.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.148 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)