

Product datasheet

Specifications



Universal dimming actuator REG-K/230/1000 W, light grey

MTN649310

! Discontinued on: May 1, 2024

! Discontinued

Main

Range Of Product	KNX
Product Or Component Type	Dimming actuator
Operating Mode	KNX bus system Manual
Bus Type	KNX

Complementary

Total Number Of 18 Mm Modules	4
Mounting Support	DIN rail
[Ue] Rated Operational Voltage	110...230 V
Network Frequency	50/60 Hz
Input Type	1 x push-button: 230 V AC 1 x electronic push-button: 230 V AC
Number Of Outputs	1
Local Signalling	LED
Load Type	Incandescent lamps: 30...1000 W at 230 V 50 Hz AC Incandescent lamps: 30...850 W at 230 V 60 Hz AC Incandescent lamps: 14...480 W at 110 V 50 Hz AC Incandescent lamps: 14...400 W at 110 V 60 Hz AC Inductive: 50...1000 W at 230 V 50 Hz AC Inductive: 50...850 W at 230 V 60 Hz AC Inductive: 24...480 W at 110 V 50 Hz AC Inductive: 24...400 W at 110 V 60 Hz AC Capacitive: 50...1000 W at 230 V 50 Hz AC Capacitive: 50...850 W at 230 V 60 Hz AC Capacitive: 24...480 W at 110 V 50 Hz AC Capacitive: 24...400 W at 110 V 60 Hz AC

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	12.5 cm
Package 1 Length	16.0 cm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight	281.9 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.337 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)