

# Product datasheet

Specifications

## Actassi 19-C Evolution Fibre Optic Panel Sliding 19" 1U



VDIG150991V2

### Main

Range Of Product	Actassi
Product Or Component Type	19" fibre optic panel
Provided Equipment	1 transparent cover rear 2 quick fix 19" mounting 2 coiling wheel 2 transparent cover front 2 Pg 9 cable gland 3 blanking plate 4 label holder 2 pop rivet
Colour	Dark grey (RAL 7016)

### Complementary

Product Compatibility	3 adaptor plate
Device Composition	without connectors
Number Of Connectors	24
Number Of Optic Fibre	48
Number Of Rack Unit	1U
Material	DC01 1.2 mm metal sheet PA6 plastic part PA66 GF20 plastic part PC plastic part PMMA (polymethyl methacrylate) plastic part
Height	45 mm
Width	490 mm
Depth	300 mm
Net Weight	4.7 kg
Targeted Region	Europe Asia Pacific.

### Environment

Ambient Air Temperature For Operation	-10...55 °C
Standards	IEC 60297 NF C 20-150

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	5.700 cm
Package 1 Width	34.500 cm
Package 1 Length	55.000 cm
Package 1 Weight	3.945 kg
Unit Type Of Package 2	S06
Number Of Units In Package 2	18
Package 2 Height	73.500 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	84.640 kg

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



## Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations