


# Product datasheet

Specifications



## Actassi CL-MNC6A Patchcord S/ FTP 4P Cat6A 550MHz LSZH 10m Grey

VDIP185X46100

⚠ Discontinued on: Sep 4, 2023

⚠ To be end-of-service on: Sep 3, 2025

⚠ Discontinued

### Main

Range	Actassi
Product	Patch cord
Colour	Patchcord: grey
Quantity Per Set	1
Cable Shielding Type	S/FTP
Provided Component	Grey coloured clips Green coloured clips Red coloured clips

### Complementary

Product Compatibility	Coloured clips red Coloured clips green Coloured clips yellow Coloured clips blue
Length (Customizable Value In Configurator)	0...10 m
Communication Network Type	10GBASE-T
Connector Type	RJ45
Communication Network Category	6 <sub>A</sub>
Transmission Frequency	550 MHz
Awg Gauge	AWG 26
Input Impedance	100 Ohm
Material	Solid bare copper: conductor PE (polyethylene): wire insulation
Targeted Region	Europe

### Environment

Ambient Air Temperature For Installation	0...50 °C
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...60 °C
Temperature Resistance	60 °C
Flame Retardance	LSZH
Product Certifications	Delta

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EIA/TIA-568-C.2 ISO/IEC 11801:2011 Ed.2.2 EN 50173 Ed.3 IEC 61935-2
-----------	--

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	18 cm
Package 1 Length	18 cm
Package 1 Weight	396 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile		No need of specific recycling operations