
# **Product datasheet**





### FRONT PLATE INF32/40 3P VERTICAL WIDTH 600/650 3M

03312

! Discontinued on: 28 Feb 2021



#### Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	FuPact: fixed INF32 - control: extended rotary handle - vertical installation FuPact: fixed INF40 - control: extended rotary handle - vertical installation
Poles Description	4 x 3P: mounting plate support: INF32 vertical installation 4 x 3P: mounting plate support: INF40 vertical installation
Operating Position	Vertical

### Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	3
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	150 mm
Width	500 mm
Net Weight	0.66 kg
Quantity Per Set	Set of 1

Life Is On Schneider 26 Apr 2024

#### Functional Unit 600 mm Prisma G floor-standing enclosure FuPact INF32 fixed extended rotary

handle vertical 3P 4 direct 3

600~mm Prisma G wall-mounted enclosure FuPact INF32 fixed extended rotary handle vertical 3P 4 direct 3

600~mm Prisma G floor-standing enclosure FuPact INF40 fixed extended rotary handle vertical 3P 4 direct 3

600 mm Prisma G wall-mounted enclosure FuPact INF40 fixed extended rotary handle vertical 3P 4 direct 3  $\,$ 

650 mm 400 mm Prisma P cubicle FuPact INF32 fixed extended rotary handle

vertical 3P 4 direct 3

650 mm 400 mm Prisma P cubicle FuPact INF40 fixed extended rotary handle vertical 3P 4 direct 3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	16 cm
Package 1 Length	51 cm
Package 1 Weight	660 a



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile