
Product datasheet

Specifications






PLAIN FRONT PLATE WIDTH 600/650 6M

03806

! Discontinued on: 30 Sept 2022



Main

Range	Prisma	
Range Of Product	Prisma G Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle	
Type Of Front Plate	t Plate Plain	
Installed Device	Power meters: kilowatt-hour meters - vertical installation connection Altistart: ATS01N	
Poles Description	Description 3 x 2P: mounting plate support: kilowatt-hour meters vertical installation 2 x 4P: mounting plate support: kilowatt-hour meters vertical installation	

Complementary

Complementary	
Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm
Number Of Vertical Modules [50 Mm]	6
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	300 mm
Width	500 mm
Net Weight	1.22 kg
Quantity Per Set	Set of 1

Functional Unit	600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters
	vertical 2P 3 6
	600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters vertical 2P 3 6
	600 mm Prisma G floor-standing enclosure connection 2 6
	600 mm Prisma G wall-mounted enclosure connection 2 6
	650 mm 400 mm Prisma P cubicle connection 2 6
	600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters vertical 4P 2 6
	600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters vertical 4P 2 6
	650 mm 400 mm Prisma P cubicle power meters kilowatt-hour meters vertical 2P 3 6 650 mm 400 mm Prisma P cubicle power meters kilowatt-hour meters vertical 4P 2 6 600 mm Prisma G floor-standing enclosure Altistart ATS01N 9 6
	600 mm Prisma G wall-mounted enclosure Altistart ATS01N 9 6
	600 mm Prisma G floor-standing enclosure Altistart ATS01N 2 6
	600 mm Prisma G wall-mounted enclosure Altistart ATS01N 2 6
	650 mm 400 mm Prisma P cubicle Altistart ATS01N 9 6
	650 mm 400 mm Prisma P cubicle Altistart ATS01N 2 6

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	31.000 cm
Package 1 Length	52.000 cm
Package 1 Weight	1.250 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16.500 cm
Package 2 Width	32.400 cm
Package 2 Length	52.500 cm
Package 2 Weight	12.600 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	180
Package 3 Height	48.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	226.440 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile