



### Main

Range	Prisma
Range of product	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma P cubicle
Installation description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 800 mm
Installed device	ComPact: fixed NS1250 - control: toggle - vertical installation ComPact: fixed NS1250 - control: direct front rotary handle - vertical installation ComPact: fixed NS1250 - control: motor mechanism - vertical installation ComPact: fixed NS1600 - control: toggle - vertical installation ComPact: fixed NS1600 - control: direct front rotary handle - vertical installation ComPact: fixed NS1600 - control: motor mechanism - vertical installation ComPact: fixed NS630b...1000 - control: toggle - vertical installation ComPact: fixed NS630b...1000 - control: direct front rotary handle - vertical installation ComPact: fixed NS630b...1000 - control: motor mechanism - vertical installation
Poles description	1 x 3P: fixed NS1250 vertical installation 1 x 4P: fixed NS1250 vertical installation 1 x 3P: fixed NS1600 vertical installation 1 x 4P: fixed NS1600 vertical installation 1 x 3P: fixed NS630b...1000 vertical installation 1 x 4P: fixed NS630b...1000 vertical installation
Number of vertical modules [50 mm]	17 module(s): NS1250, front connection on Canalis in 650 mm Widecubicle 16 module(s): NS1250, rear connection on Canalis in 650 mm Widecubicle 14 module(s): NS1250, front connection on adaptor in 650 mm Widecubicle 10 module(s): NS1250, rear connection on adaptor in 650 mm Widecubicle 16 module(s): NS1600, rear connection on Canalis in 650 mm Widecubicle 14 module(s): NS1600, front connection on adaptor in 650 mm Widecubicle 10 module(s): NS1600, rear connection on adaptor in 650 mm Widecubicle 17 module(s): NS630b...1000, front connection on Canalis in 650 mm Widecubicle 16 module(s): NS630b...1000, rear connection on Canalis in 650 mm Widecubicle 12 module(s): NS630b...1000, front connection on adaptor in 650 mm Widecubicle 10 module(s): NS630b...1000, rear connection on adaptor in 650 mm Widecubicle
Standards	IEC 61439-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product certifications	ASEFA
------------------------	-------

## Complementary

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Smooth
Colour	White (RAL 9001)
Width	650 mm
Height	300 mm
Net weight	3.08 kg
Functional unit	<p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed toggle vertical 3P 1 front connection on Canalis 17 387.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed direct front rotary handle vertical 3P 1 front connection on Canalis 17 387.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed toggle vertical 3P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed direct front rotary handle vertical 3P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed toggle vertical 3P 1 front connection on adaptor 14 237.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 14 237.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 3P 1 front connection on Canalis 17 387.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 3P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 3P 1 front connection on adaptor 14 237.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed toggle vertical 4P 1 front connection on Canalis 17 387.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed direct front rotary handle vertical 4P 1 front connection on Canalis 17 387.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed toggle vertical 4P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed direct front rotary handle vertical 4P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed toggle vertical 4P 1 front connection on adaptor 14 237.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 14 237.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 4P 1 front connection on Canalis 17 387.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 4P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 4P 1 front connection on adaptor 14 237.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed toggle vertical 3P 1 rear connection on adaptor 10 37.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed toggle vertical 4P 1 rear connection on adaptor 10 37.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed direct front rotary handle vertical 3P 1 rear connection on adaptor 10 37.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed direct front rotary handle vertical 4P 1 rear connection on adaptor 10 37.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 3P 1 rear connection on adaptor 10 37.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 4P 1 rear connection on adaptor 10 37.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1600 fixed toggle vertical 3P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1600 fixed direct front rotary handle vertical 3P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1600 fixed toggle vertical 3P 1 front connection on adaptor 14 237.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1600 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 14 237.5 mm</p> <p>650 mm 800 mm Prisma P cubicle ComPact NS1600 fixed motor mechanism vertical 3P 1 rear connection on Canalis 16 337.5 mm</p> <p>650 mm 400 mm Prisma P cubicle ComPact NS1600 fixed motor mechanism vertical 3P 1 front connection on adaptor 14 237.5 mm</p>



## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.2 kg
Package 1 Height	4.5 cm
Package 1 width	30.5 cm
Package 1 Length	58 cm
Unit Type of Package 2	S04
Number of Units in Package 2	7
Package 2 Weight	22.32 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm
Unit Type of Package 3	P12
Number of Units in Package 3	84
Package 3 Weight	267.84 kg
Package 3 Height	80 cm
Package 3 width	80 cm
Package 3 Length	120 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Halogen content performance	Halogen free product