# **Product datasheet**

Specification



## FR.PL.HZ.INS250



! Discontinued on: 14 May 2023

① Discontinued

#### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed INS250 - control: direct front rotary handle - horizontal installation ComPact: fixed INV250 - control: direct front rotary handle - horizontal installation
Poles Description	1 x 3P: mounting plate support: INS250 horizontal installation 1 x 4P: mounting plate support: INS250 horizontal installation 1 x 3P: mounting plate support: INV250 horizontal installation 1 x 4P: mounting plate support: INV250 horizontal installation
Operating Position	Horizontal

## Complementary

Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	500 mm
Net Weight	0.82 kg
Quantity Per Set	Set of 1

**Functional Unit** 650 mm 400 mm Prisma P cubicle ComPact INS250 fixed direct front rotary handle

horizontal 3P 1 direct 4

650 mm 400 mm Prisma P cubicle ComPact INS250 fixed direct front rotary handle

horizontal 4P 1 direct 4

650 mm 400 mm Prisma P cubicle ComPact INV250 fixed direct front rotary handle

horizontal 3P 1 direct 4

650 mm 400 mm Prisma P cubicle ComPact INV250 fixed direct front rotary handle horizontal 4P 1 direct 4

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	21.0 cm
Package 1 Length	51.0 cm
Package 1 Weight	784.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	22.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	8.44 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	180
Package 3 Height	48.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	163.92 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	
China Rons Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	
Environmental Disclosure	Product Environmental Profile
Circularity Profile	Find of Utility Information
Officiality 1 forme	End of Life Information