




Actassi - cable - category 3 - 25 pair - UTP - 305 m/reel - grey - CM

ACT25P3UCM3RGY

! Discontinued on: 2 Apr 2021



Main

Range	Actassi
Product Or Component Type	Copper cable
Colour Tint	Grey
Cable Shielding Type	U/UTP

Complementary

Type Of Cable	Multipair cable	
Communication Network Category	3	
Minimum Return Loss	Guaranteed: 12 dB at 0.772 MHz	
	Guaranteed: 12 dB at 1 MHz	
	Guaranteed: 12 dB at 4 MHz	
	Guaranteed: 12 dB at 8 MHz	
	Guaranteed: 12 dB at 10 MHz	
	Guaranteed: 10 dB at 16 MHz	
Attenuation	Guaranteed: 2.2 dB @ 0.772 MHz	
	Guaranteed: 2.6 dB @ 1 MHz	
	Guaranteed: 5.6 dB @ 4 MHz	
	Guaranteed: 8.5 dB @ 8 MHz	
	Guaranteed: 9.7 dB @ 10 MHz	
	Guaranteed: 13.1 dB @ 16 MHz	
Near End Crosstalk [Next]	Guaranteed: 43 dB at 0.772 MHz	
	Guaranteed: 41 dB at 1 MHz	
	Guaranteed: 32 dB at 4 MHz	
	Guaranteed: 28 dB at 8 MHz	
	Guaranteed: 26 dB at 10 MHz	
	Guaranteed: 23 dB at 16 MHz	
Maximum Loop Resistance	93.8 Ohm	
Capacitance Unbalance	330 pF / 100 m	
Wire Insulation Material	PE	
Awg Gauge	AWG 24	
Cable Outer Diameter	11 mm	
Cable Length	305 m	

Environment

Ambient Air Temperature For Operation	-2060 °C
Flame Retardance	СМ
Standards	ANSI/TIA/EIA-568-B

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile