Product datasheet

Specifications





Switch, AvatarOn, 2-pole 1-way, LED, brass terminal, IP20, white

E8331D20N_WE_C5

Main

Product Or Component Type	Switch	
Device Application	Control	
Load Type	Resistive Incandescent lamp Fluorescent lamps Serial boost load (SBL) Small motor load	
Colour Tint	White	

Complementary

Complete product	
20 A at 250 V AC 50/60 Hz	
2-pole 1-way	
1 gang	
1	
Capacity 3 x 2.5 mm² for stranded cable(s) 1 x 4 mm² for stranded cable(s) 1 x 6 mm² for stranded cable(s)	
Brass terminal	
On: LED indicator, LED (amber)	
Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator	
Flush	
86 mm	
86 mm	
32 mm	

Environment

Ip Degree Of Protection	IP20
Maximum Ambient Air Temperature For Operation	45 °C
Operating Altitude	2000 m
Relative Humidity	095 %
Environmental Characteristic	UV resistant

 Standards
 IEC 60669-1

 MS IEC 60669-1

BS EN 60669-1 SS 227-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	103.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.205 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	7230.0 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations