Product datasheet

Specifications





current transformer tropicalised DIN mount 60 5 for cables d. 21

METSECT5CC006

Main

Range	PowerLogic
Product Name	CT
Product Or Component Type	Current transformer
Secondary Current	5 A
Accuracy Class	Class 1 at 1.25 VA Class 3 at 2 VA
[In] Rated Current	60 A

Complementary

· · · · · · · · · · · · · · · · · ·	
Current Transformer Type	Tropicalised for cable
Current Transformer Ratio	60/5
[Ith] Conventional Free Air Thermal Current	3.6 kA
Dynamic Withstand Current	2.5 lth
Maximum Safety Factor	5
[Ue] Rated Operational Voltage	< 720 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	3 kV
Mounting Mode	Clip-on By screws
Mounting Support	Mounting plate DIN rail
Width	44 mm outside:
Height	65 mm outside:
Depth	30 mm frame: 37 mm total:
Diameter	21 mm
Net Weight	0.19 kg
[Uimp] Rated Impulse Withstand Voltage	3 kV
Electrical Insulation Class	Class B
Cable Outer Diameter	21 mm
Sealing	With

Environment

Standards

IEC 61869-2 VDE 0414

Product Certifications	CE
Ip Degree Of Protection	IP20
Relative Humidity	095 %
Ambient Air Temperature For Operation	-2560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	5.5 cm
Package 1 Length	8.2 cm
Package 1 Weight	198.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	10.07 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration