

# Product datasheet

Specifications



## Airing grille cut-out diameter 33mm IP45

NSYCAG33LP

### Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	Thalassa Thalassa PLS Thalassa Thalassa PLM Thalassa Thalassa TBS
Product Or Component Type	Plastic ventilation louvre
Accessory / Separate Part Category	Thermal management accessory
Accessory / Separate Part Destination	ClimaSys ventilation system
Mounting Position	Vertical
Fixing Mode	By screws
Device Composition	2 plastic louvre

### Complementary

Material	Polyamide 6
Colour	Grey (RAL 7035)
Cut-Out Dimensions	33 mm
Height	69 mm external:
Width	47 mm external:
Depth	22.5 mm external:
Ip Degree Of Protection	IP44

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	4.500 cm
Package 1 Length	7.000 cm
Package 1 Weight	26.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	4.000 cm
Package 2 Width	4.500 cm

Package 2 Length	7.000 cm
Package 2 Weight	57.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	500
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	14.950 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

**Reach Regulation**

[REACH Declaration](#)

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

**China Rohs Regulation**

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

**Environmental Disclosure**

[Product Environmental Profile](#)

**Circularity Profile**

No need of specific recycling operations