Product datasheet

Specifications



Cable passage IP65 w/o connectors, 29 entries.

NSYTSA2429SE

() Discontinued on: 31 Dec 2022

Main

Range	Spacial
Product Or Component Type	Quick entrance plate
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure Spacial Spacial S3CM control enclosure Spacial Spacial SBM industrial box Thalassa Thalassa PLA suitable enclosure Thalassa Thalassa PHD suitable enclosure Thalassa Thalassa PLM compact enclosure Thalassa Thalassa PLS insulating modular box Spacial Spacial S3HD compact enclosure
Device Composition	1 fixing elements 1 plate
Quantity Per Set	Set of 1

Complementary

Mounting Support	Body of enclosure Cable gland plate	
Material	Polyamide	
Fixing Mode	By fixing element	
Total Cable Entry Number	29	
Cable Entry Number	29 x 36.5 mm	
Height	14 mm real:	
Width	146 mm real: 112 mm cut-out: 130 mm fixing center:	
Depth	58 mm real: 36 mm cut-out: 32 mm fixing centre:	
Net Weight	0.16 kg	

Environment

Ip Degree Of Protection

IP65

Packing Units

Unit Type Of Package 1

PCE

Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8 cm
Package 1 Length	17 cm
Package 1 Weight	148 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	20 cm
Package 2 Width	20 cm
Package 2 Length	30 cm
Package 2 Weight	1.7 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	100
Package 3 Height	37 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	183 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations