# **Product datasheet**

Specifications





Ulti - 250V 16 AX - 2 gang - 2 way - impress switch module - blue LED

U202SPM\_2\_B00

! Discontinued on: 30 Jun 2023

(!) Discontinued

#### Main

Range	Ulti
Device Application	Control
Product Or Component Type	Switch module
Load Type	Fluorescent
Switch Application	Switch

## Complementary

Bulb Type	LED blue	
Rated Current	16 AX at 250 V AC 50 Hz	
Number Of Cables	3 cable(s) 2.5 mm <sup>2</sup>	
Opening Distance	> 3 mm	
Device Mounting	Flush	
Fixing Mode	By screws	
Distance Between Centers	60.3 mm	
Number Of Gangs	2 gangs	
Switch Function	2-way	
Width	87 mm	
Height	87 mm	
Depth	23.3 mm	

## **Environment**

Ambient Air Temperature For Operation	035 °C
Relative Humidity	095 %
Standards	BS EN 60669-1
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.1 cm

Package 1 Width	8.4 cm
Package 1 Length	8.6 cm
Package 1 Weight	185.2 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	18 cm
Package 2 Width	31.2 cm
Package 2 Length	56.3 cm
Package 2 Weight	5556 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	600
Package 3 Height	100 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	111120 g



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations