Product datasheet

Specifications





Acti9 - MIN - electromechanical timer - adjustable from 1 to 7 minutes

15363

Main

Range Of Product	Acti9
Product Name	Acti9 MIN
Device Short Name	MIN
Product Or Component Type	Electromechanical timer
Colour Tint	White (RAL 9003)

Complementary

Device Application	Building
Load Type	Parallel-corrected fluorescent tube 14 x 40 W 4.7 µF Parallel-corrected fluorescent tube 10 x 58 W 7 µF Parallel-corrected fluorescent tube 3.0 x 100 W 18 µF 230 V AC halogen lamp 2300 W 230 V AC incandescent lamp 2300 W Fluocompact lamp 2300 VA Compact fluorescent lamp 21 x 7 W Compact fluorescent lamp 13 x 11 W Compact fluorescent lamp 10 x 15 W Compact fluorescent lamp 7 x 20 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W
Power Consumption In Va	1 VA
Maximum Switching Current	16 A - 230 V AC pf = 1
[Ue] Rated Operational Voltage	230 V AC at 50 Hz
Time Delay	Adjustable from 1 to 7 minutes
Mounting Support	DIN rail
9 Mm Pitches	2
Connections - Terminals	Screw terminals - <= 6 mm ²
Width	18 mm
Height	83 mm
Depth	68 mm
Net Weight	84 g

Environment

Ambient Air Temperature For Operation	-1050 °C
Ip Degree Of Protection	IP20 B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	7 cm
Package 1 Length	9.9 cm
Package 1 Weight	82 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7.5 cm
Package 2 Width	10.5 cm
Package 2 Length	22 cm
Package 2 Weight	865 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	110
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	10.033 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information