



auxiliary contact - 1 SD - 380..415 V - 6 A - for C60

26927

- ! Discontinued on: Sep 30, 2020
- ! End-of-service on: Jun 30, 2021

(!) Discontinued

Main

Range Of Product	Multi9
Product Or Component Type	Fault contact
Device Short Name	SD
Signal Contacts Composition	1 C/O
[In] Rated Current	AC-12 3 A at 380415 V, AC 50/60 Hz
	AC-12 6 A at 220240 V, AC 50/60 Hz
	DC-12 1 A at 130 V, DC
	DC-12 1.5 A at 60 V, DC
	DC-12 2 A at 48 V, DC
	DC-12 6 A at 24 V, DC
9 Mm Pitches	1

o min i itenes

Complementary

Mounting Mode	Fixed	
Mounting Support	DIN rail	
Height	84 mm	
Width	9 mm	
Depth	73 mm	
Connections - Terminals	Clamp terminal2 cable(s) 1.5 mm² - flexible Clamp terminal2 cable(s) 1.5 mm² - rigid Clamp terminal1 cable(s) 0.52.5 mm² - flexible Clamp terminal1 cable(s) 0.52.5 mm² - rigid	
Wire Stripping Length	9 mm	
Tightening Torque	1 N.m	

Environment

Standards	EN/IEC 60947-5-1
Product Certifications	ASTA KEMA ASEFA LCIE
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1
Pollution Degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2550 °C

Ambient Air Temperature For -40...85 °C Storage

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	8 cm
Package 1 Length	8.7 cm
Package 1 Weight	38 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information