Product datasheet

Specifications





control unit Micrologic 2.0, Masterpact NT 06/16 fixed, LI protections

65296

Main

Range	MasterPact
Range Of Product	MasterPact NT
Product Or Component Type	Control unit
Trip Unit Name	MicroLogic 2.0
Trip Unit Technology	Electronic
Range Compatibility	Masterpact NT0616
Device Application	Distribution
Number Of Poles	4P 3P
Protected Poles Description	4t 3t 3t + N/2
Trip Unit Protection Functions	Basic protection
Protection Type	for overload protection (long time) for instantaneous short-circuit protection
Trip Unit Rating	630 A at 50 °C 800 A at 50 °C 1000 A at 50 °C 1250 A at 50 °C 1600 A at 50 °C
Network Type	AC
Network Frequency	50/60 Hz
Circuit Breaker Mounting Mode	Fixed

Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.41 x ln
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	0.716.6 s at 7.2 x lr 0.524 s at 6 x lr 12.5600 s at 1.5 x lr
Thermal Memory	20 mn
Instantaneous Protection Pick-Up Adjustment Type li	Adjustable 9 settings
[li] Instantaneous Protection Pick- Up Adjustment Range	1.510 x lr
Earth-Leakage Protection	Without

Zone Selective Interlocking Zsi	Without
Local Signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error

Environment

Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	8.0 cm
Package 1 Length	21.5 cm
Package 1 Weight	318.0 g

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information