



End feed unit, Canalis KNA, 40/63A, right or left mounting, polarity 3L+N+PE/3L+PEN, white **RAL9001**

KNA63AB4

Main

Range Of Product	Canalis	
Product Name	KN	
Device Short Name	KNA	
Product Compatibility	Canalis KNA busbar trunking 4063 A	
Product Or Component Type	Feed unit	
Conductors Material	Aluminium	
[le] Rated Operational Current	63 A	
[Ue] Rated Operational Voltage	230500 V	
Number Of Circuits	1	
Busbar Trunking Polarity	nking Polarity 3L + N + PE L + N + PE	
Protection Type	Without protection	
Control Type	Without	
Colour	White (RAL 9001)	

Complementary

Provided Equipment	End cover	
Mounting Location	Left Right	
Mounting Mode	By clips	
Mounting Support	Busbar	
Connections - Terminals	Terminal block for 16 mm² flexible Terminal block for 25 mm² rigid	
Width	265 mm	
Depth	71 mm	
Height	92 mm	
Net Weight	580 g	
Standards	IEC 61439-6	

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	11.000 cm
Package 1 Length	29.900 cm
Package 1 Weight	650.000 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	36
Package 2 Height	37.400 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	29.818 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations