

Product datasheet

Specifications



outlet grille plast cut out
223x223mm ext dim 268x248mm
IP54

NSYCAG223LPF

Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	Prisma Prisma P ClimaSys ClimaSys CV fan
Product Or Component Type	Outlet grille
Accessory / Separate Part Category	Thermal management accessory
Accessory / Separate Part Destination	ClimaSys ventilation system
Fixing Mode	By screws Clipped
Device Composition	1 support frame 1 external part 1 G2 M1 synthetic standard filter

Complementary

Material	Injected thermoplastic (ASA PC)
Colour	External part: grey (RAL 7035)
Cut-Out Dimensions	223 x 223 mm
Height	External: 268 mm
Width	External: 248 mm
Depth	18 mm external:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	25.5 cm
Package 1 Length	28 cm
Package 1 Weight	533 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	40 cm
Package 2 Width	30 cm
Package 2 Length	40 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	5.33 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	240
Package 3 Height	131 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	143 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations