

# Product datasheet

Specifications



## Ulti - 250V 16 AX - 4 gang - 1 way - impress switch module - blue LED

U204SPM\_1\_B00\_G3

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	Ulti
Device Application	Control
Product Or Component Type	Switch module
Load Type	Fluorescent
Switch Application	Switch

### Complementary

Bulb Type	LED blue
Rated Current	16 AX at 250 V AC 50 Hz
Number Of Cables	3 cable(s) 2.5 mm <sup>2</sup>
Opening Distance	> 3 mm
Device Mounting	Flush
Fixing Mode	By screws
Distance Between Centers	60.3 mm
Number Of Gangs	4 gangs
Switch Function	1-way
Width	87 mm
Height	87 mm
Depth	23.3 mm

### Environment

Ambient Air Temperature For Operation	0...35 °C
Relative Humidity	0...95 %
Standards	BS EN 60669-1
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	12.2 cm
Package 1 Length	12.2 cm
Package 1 Weight	99 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	18 cm
Package 2 Width	31.2 cm
Package 2 Length	56.3 cm
Package 2 Weight	8564 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	600
Package 3 Height	105 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	69258 g

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations