

Product datasheet

Specifications



Vijeo Designer 6.2 , USB cable HMI configuration software single license

VJDSUDTGAV62M

⚠ Discontinued on: Mar 22, 2022

⚠ To be discontinued

Main

Range Of Product	Vijeo Designer
Product Or Component Type	Configuration software
Format	DVD-ROM
Type Of License	Single (1 station)
Product Compatibility	SoMachine V4.1 or higher
Software Version	V6.2
Operating System Requirement	Windows 7 Professional 32/64 bit Windows 8.1 Windows 10 Professional 32/64 bit
Language	Chinese Italian English German Portuguese French Spanish

Complementary

Provided Equipment	Acrobat Reader 1 cable USB Tutorial in flash format Vijeo Designer software User's documentation in electronic format
Audio Video Coding Standard	JPEG
Communication Port Protocol	Profibus DP UniTE TCP/IP Fipio/Fipway USB Modbus TCP master Modbus RTU master ELAU PacDrive MELSEC Simatic Modbus 32-bit extensions ROC Plus Sysmacway Allen-Bradley Uni-Telway Toyopuc PC3J Ethernet/IP Explicit Modbus Plus
Previous Software Version	V6.1
Software Designation	Vijeo Designer

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Software Function	4 asian alphabets 2 middle eastern alphabets 9999 alarms 8000 variables 34 western alphabets Sharing up to 300 variables
Range Compatibility	Harmony XBT GK Harmony STO & STU Harmony XBT GT Harmony Compact iPC Harmony GTU Harmony iPC Harmony XBT GH Harmony GTO Harmony Smart Harmony XBT GTW

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.200 cm
Package 1 Width	14.000 cm
Package 1 Length	16.500 cm
Package 1 Weight	308.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	12
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---------------------------------------------------------------------------------------------------

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	-------------------------------------------------------------------------------------------------------------