

Product datasheet

Specifications



APC Home/Office SurgeArrest 6 outlets with Phone Protection 230V Germany

PH6T3-GR

Discontinued on: Oct 5, 2022

Discontinued

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	230 V
Input Connection Type	Schuko CEE 7/7P
Cable Length	2.44 m
Number Of Cables	1
Provided Equipment	2 x 1.8 m telephone cables User manual

Physical

Colour	Charcoal
Height	30.5 cm
Width	12.2 cm
Depth	4.2 cm
Net Weight	1.02 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current	10 A
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Number Of Power Socket Outlets	6
Outlet Standard	Schuko CEE 7

Conformance

Product Certifications	CE
Equipment Protection Policy	Lifetime : 75000 euros

Environmental

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...50000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m

Surge Protection and Filtering

Ep Joule Rating	2350 J
Data Line Protected	1-4 RJ11 / 3-6 RJ45
Response Time	0 ns common mode
Common Mode Rejection	50 dB
Peak Current	48 kAcommon mode 26 kAnormal mode
Surge Energy Rate	2030 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	31.1 cm
Package 1 Width	5.2 cm
Package 1 Length	21.1 cm
Package 1 Weight	1.06 kg
Number Of Units In Package 2	12
Package 2 Length	657.35 mm
Package 2 Weight	13.61 kg
Number Of Units In Package 3	120
Scc14	10731304223815

Contractual warranty

Warranty	5 years (all other countries), Limited Lifetime (European Union countries only)
----------	---

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
Environmental Disclosure		Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile		End of Life Information