



120mm Rotating Mirror Blue 24VAC-DC

XVR12B06S

Main

Range Of Product	Harmony XVR	
Product Or Component Type	Prewired rotating mirror beacon	
Sound Signalling	Buzzer	
Device Short Name	XVR	
Mounting Diameter	120 mm	
Ip Degree Of Protection	IP23 conforming to IEC 60529	
[Us] Rated Supply Voltage	24 V AC/DC	
Light Source	High luminosity LED, blue	
Noise Level	5090 dB (continuous or intermittent tone) at 1 m	

Complementary

Material	ABS (acrylonitrile butadiene-styrene): body part AS: globe
Cad Overall Width	120 mm
Cad Overall Depth	120 mm
Net Weight	0.5 kg
Marking	CE
Product Mounting	By 3 M5 screws
Supply Voltage Limits	1930 V DC 21.626.4 V AC
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	196 mA
Flashing Frequency	2.3 Hz
Clamping Connection Capacity	0.83 mm²
Awg Gauge	AWG 18
Cable Length	400 mm

Environment

Standards	IEC 61000-6-4 IEC 61000-6-2
Protective Treatment	TC
Ambient Air Temperature For Storage	-3570 °C
Ambient Air Temperature For Operation	-1050 °C

Electrical Shock Protection Class Class II conforming to IEC 61140

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.5 cm
Package 1 Width	13.8 cm
Package 1 Length	14 cm
Package 1 Weight	617 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	6.577 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


XVR12B06S

Dimensions Drawings

Rotating Mirror Beacon

Dimensions






Product datasheet

XVR12B06S

Mounting and Clearance

Rotating Mirror Beacon

Panel Cut-out



Apr 25, 2024