



Empty control station, Harmony XALE, plastic, light grey, 1 cut out, for Harmony XB7

XALE1

! Discontinued on: Aug 27, 2020

(!) Discontinued

#### Main

Range Of Product	Harmony XALE
Product Or Component Type	Empty control station
Device Short Name	XALE
Product Destination	For XB7 Ø 22 mm control and signalling units
Number Of Cut-Out	1 cut-out
Colour Of Base Of Enclosure	Light grey (RAL 7035)
Colour Of Cover	Light grey (RAL 7035)
Material	ABS (acrylonitrile butadiene-styrene)
Cable Entry	2 knock-outs, clamping capacity: 16 mm 4 knock-outs for ISO M20
Sale Per Indivisible Quantity	5
Ip Degree Of Protection	IP54 conforming to IEC 60529

# Complementary

Assembly Style	For customer assembly
Net Weight	0.08 kg
Marking	CE

#### **Environment**

Protective Treatment	TC
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2555 °C
<b>Electrical Shock Protection Class</b>	Class II conforming to IEC 60536
Ik Degree Of Protection	IK05 conforming to EN 50102
Standards	EN/IEC 62208 EN/IEC 60947-5-1 EN/IEC 60947-5-5 EN/IEC 60947-1

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	8.200 cm
Package 1 Width	8.100 cm
Package 1 Length	11.500 cm
Package 1 Weight	72.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.300 cm
Package 2 Width	8.100 cm
Package 2 Length	31.300 cm
Package 2 Weight	414.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	45
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.200 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

# XALE1

#### **Dimensions Drawings**

#### **Dimensions**

mm in.



- (1) 4 ISO 20 knock-outs.
- (2) 2 knock-outs for cable entry, maximum capacity 16 mm / 0.63 in.
- (3) 2 knock-out elongated fixing holes  $\emptyset$  3 mm x 5 mm /  $\emptyset$  0.12 in. x 0.20 in.

Control station XALE fitted with:	c in mm	c in in.
Flush pushbutton	61	2.40
Projecting pushbutton	63	2.48
Illuminated pushbutton	66.5	2.62
Pilot light	63	2.48
Emergency stop without key	81.5	3.21
Selector switch with standard handle	76.5	3.01
Key switch	92	3.62