

Lembar data produk

Spesifikasi



non - adjustable time delay relay
for voltage release MN - 200/250 V
AC/DC

33685

Main

Device Short Name	MN delay unit
Product Or Component Type	Time delay relay
Device Application	Control
Range Compatibility	Masterpact MasterPact NT Masterpact MasterPact NW ComPact ComPact NS630b...1600 ComPact ComPact NS1600b...3200 Masterpact MasterPact NW UL 489 Masterpact MasterPact NT UL 489 Masterpact MasterPact NW DC
Voltage Release Type	Undervoltage release
[Uc] Control Circuit Voltage	200...250 V AC 50/60 Hz 200...250 V DC

Complementary

Impulse Duration	200 ms
Time Delay Range	0.25 s
Threshold Tripping Voltage	0.35...0.7 Un open 0.85 Un close
Supply Holding Power	4.5 VA
Supply Inrush Power	200 VA
Mounting Mode	External mounting
Response Time	0.25 s
Accessory / Separate Part Category	Spare part for Compact NS630b...1600 Spare part for Compact NS1600b...3200

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	8.0 cm
Package 1 Length	9.0 cm
Package 1 Weight	147.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	36
Package 2 Height	30.0 cm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.73 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Sertifikasi & Standar

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)