

Lembar data produk

Spesifikasi



Domae - comb busbar - 1L - 18 mm pitch - 57 modules - 63A



10388

⚠ Telah dihentikan pada: 31 Jul 2023

⚠ Dihentikan

Main

Range	Domae
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	1L
Length In 18 Mm Modules	57

Complementary

Number Of Ways	57 ways 1 L
Poles Configuration For 1 Way	1 x 1P
Connection Pitch	18 mm
Connector Type	Tooth
Distance Between Way	18 mm
Insulation	Insulated
Device Presentation	Cuttable
[Ie] Rated Operational Current	63 A at 40 °C
[Ue] Rated Operational Voltage	230 V AC Ph/N
[Ui] Rated Insulation Voltage	500 V AC conforming to IEC 61439-1
Mounting Location	Top on tunnel type terminals
9 Mm Pitches	114
Width	1000 mm
Colour	Light grey (RAL 7035)
Range Compatibility	Easy9 Easy9 MCB Easy9 Easy9 RCBO Easy9 Easy9 RCCB Easy9 Easy9 switch Domae

Environment

Standards	IEC 60664 EN/IEC 60439-1
Fire Resistance	850 °C (30 s) conforming to IEC 60695-2-1
Pollution Degree	3

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	2.5 cm
Package 1 Length	101.7 cm
Package 1 Weight	175 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	104 cm
Package 2 Width	10 cm
Package 2 Length	11 cm
Package 2 Weight	8.776 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	2700
Package 3 Height	92 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	485.904 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations