

Lembar data produk

Spesifikasi



Acti 9 - fuse-disconnector STI - 1 pole - 25 A - for fuse 10.3 x 38 mm

A9N15636

Main

Range	Acti9
Product Name	Acti9 STI
Product Or Component Type	Fuse-disconnector
Device Short Name	STI
Poles Description	1P

Complementary

[In] Rated Current	2 A 4 A 6 A 10 A 16 A 20 A 25 A
Fuse Curve	AM GG
Fuse Size	10.3 x 38 mm
[Ue] Rated Operational Voltage	500 V AC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	75 mm
Colour	White
Connections - Terminals	Screw clamp terminals1 cable(s) 0.75...10 mm² rigid Screw clamp terminals1 cable(s) 0.5...6 mm² flexible Screw clamp terminals2 cable(s) 0.75...4 mm² rigid Screw clamp terminals2 cable(s) 0.5...6 mm² flexible
Wire Stripping Length	12 mm
Tightening Torque	2 N.m

Environment

Standards	IEC 60269-1/2 IEC EN 60947-3
Ip Degree Of Protection	IP20

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Pollution Degree	3
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.800 cm
Package 1 Width	1.800 cm
Package 1 Length	8.400 cm
Package 1 Weight	55.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.600 cm
Package 2 Width	9.400 cm
Package 2 Length	22.200 cm
Package 2 Weight	710.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	9.050 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Product	

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations