

# Lembar data produk

Spesifikasi



## adjustable time delay relay for voltage release MN - 200/250 V AC/DC

33682

### Main

|                              |                                                                                                                                                                                                                                                                                                                                            |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Device Short Name            | MN delay unit                                                                                                                                                                                                                                                                                                                              |
| Product Or Component Type    | Time delay relay                                                                                                                                                                                                                                                                                                                           |
| Device Application           | Control                                                                                                                                                                                                                                                                                                                                    |
| Range Compatibility          | Masterpact MasterPact NT<br>Masterpact MasterPact NW<br>ComPact ComPact NSX<br>ComPact ComPact NS630b...1600<br>ComPact ComPact NS1600b...3200<br>PowerPact PowerPact Multistandard<br>ComPact ComPact NSXm<br>ComPact ComPact NSX DC<br>Masterpact MasterPact NW UL 489<br>Masterpact MasterPact NT UL 489<br>Masterpact MasterPact NW DC |
| Voltage Release Type         | Undervoltage release                                                                                                                                                                                                                                                                                                                       |
| [Uc] Control Circuit Voltage | 200...250 V AC 50/60 Hz<br>200...250 V DC                                                                                                                                                                                                                                                                                                  |

### Complementary

|                                    |                                                                               |
|------------------------------------|-------------------------------------------------------------------------------|
| Impulse Duration                   | 200 ms                                                                        |
| Time Delay Range                   | 0.5...3 s                                                                     |
| Threshold Tripping Voltage         | 0.35...0.7 Un open<br>0.85 Un close                                           |
| Supply Holding Power               | 4.5 VA                                                                        |
| Supply Inrush Power                | 200 VA                                                                        |
| Mounting Mode                      | External mounting                                                             |
| Response Time                      | 0.5 s<br>1 s<br>1.5 s<br>3 s                                                  |
| Accessory / Separate Part Category | Spare part for Compact NS630b...1600<br>Spare part for Compact NS1600b...3200 |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 9.0 cm |
| Package 1 Width              | 8.0 cm |
| Package 1 Length             | 9.0 cm |

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

|                              |          |
|------------------------------|----------|
| Package 1 Weight             | 166.0 g  |
| Unit Type Of Package 2       | S03      |
| Number Of Units In Package 2 | 36       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 6.463 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 12 months |
|----------|-----------|

Keberlanjutan



**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi   RoHS/REACH

## Kinerja kesejahteraan

✓

Mercury Free

✓

Rohs Exemption Information

Yes

✓

Pvc Free

## Sertifikasi & Standar

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)