


# Lembar data produk

Spesifikasi



## auxiliary contact - 1 SDE

48200

### Main

|                             |                          |
|-----------------------------|--------------------------|
| Product Or Component Type   | Auxiliary contact        |
| Device Short Name           | SDE                      |
| Range Compatibility         | Masterpact MasterPact NW |
| Signal Contacts Composition | 1 NO/NC                  |

### Complementary

|                                             |                                                                                                                      |
|---------------------------------------------|----------------------------------------------------------------------------------------------------------------------|
| Auxiliary Contacts Type                     | Standard                                                                                                             |
| Mounting Mode                               | Fixed                                                                                                                |
| [Ith] Conventional Free Air Thermal Current | 5 A                                                                                                                  |
| Breaking Capacity (A)                       | AC-12: 3 A at 690 V AC 50/60 Hz<br>DC-12: 0.15 A at 250 V DC<br>DC-12: 3 A at 24/48 V DC<br>DC-12: 0.3 A at 125 V DC |
| Minimum Load                                | 100 mA at 24 V                                                                                                       |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 3.5 cm |
| Package 1 Width              | 4.0 cm |
| Package 1 Length             | 7.3 cm |
| Package 1 Weight             | 64.0 g |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 12 months |
|----------|-----------|

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

## Keberlanjutan

**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

## Kinerja kesejahteraan

|                                                                                   |                                                                                                                       |                     |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|---------------------|
|  | Reach Free Of Svhc                                                                                                    |                     |
|  | Mercury Free                                                                                                          |                     |
|  | Rohs Exemption Information                                                                                            | <a href="#">Yes</a> |
| <b>Reach Regulation</b>                                                           | <a href="#">REACH Declaration</a>                                                                                     |                     |
| <b>Eu Rohs Directive</b>                                                          | Compliant with Exemptions                                                                                             |                     |
| <b>China Rohs Regulation</b>                                                      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |                     |