

Lembar data produk

Spesifikasi



auxiliary contact - NO/NC - 5 A - 240 V - for drawout Masterpact NW

48477

Main

Device Short Name	EF contact
Product Or Component Type	Auxiliary contact
Device Application	Control
Range Compatibility	Masterpact MasterPact NW
Signal Contacts Composition	1 NO/NC

Complementary

Auxiliary Contacts Type	Standard
Auxiliary Contacts Operation	Connected position
Mounting Mode	Drawout
[Ie] Rated Operational Current	AC-12: 6 A at 690 V AC 50/60 Hz DC-12: 0.3 A at 250 V DC DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC AC-12: 6 A at 240/380 V AC 50/60 Hz AC-12: 6 A at 480 V AC 50/60 Hz
Minimum Load	100 mA at 24 V

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	4.7 cm
Package 1 Length	14.5 cm
Package 1 Weight	36.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	22.0 cm
Package 2 Width	6.0 cm
Package 2 Length	23.0 cm
Package 2 Weight	360.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	100
Package 3 Height	30.0 cm

Disclaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna.

Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	3.9 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

✓ Reach Free Of Svhc	
✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)