

Lembar data produk

Spesifikasi



control unit Micrologic 5.0,
Masterpact NT 06/16 drawout, LSI
protections

65299

Main

Range	MasterPact
Range Of Product	MasterPact NT
Product Or Component Type	Control unit
Trip Unit Name	MicroLogic 5.0
Trip Unit Technology	Electronic
Range Compatibility	Masterpact NT06...16
Device Application	Distribution
Number Of Poles	3P 4P
Protected Poles Description	3t 3t + N/2 4t
Trip Unit Protection Functions	Selective protection
Protection Type	for short time short-circuit protection for overload protection (long time) for instantaneous short-circuit protection
Trip Unit Rating	630 A at 50 °C 800 A at 50 °C 1000 A at 50 °C 1250 A at 50 °C 1600 A at 50 °C
Network Type	AC
Network Frequency	50/60 Hz
Circuit Breaker Mounting Mode	Drawout

Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.4...1 x In
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	0.7...16.6 s at 7.2 x Ir 0.5...24 s at 6 x Ir 12.5...600 s at 1.5 x Ir
Thermal Memory	20 mn
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Protection Pick-Up Adjustment Range	1.5...10 x Ir
Short-Time Protection Delay Adjustment Type Tsd	Adjustable

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

[Tsd] Short-Time Protection Delay Adjustment Range	0...0.4 s I ² t=off 0.1...0.4 s I ² t=on
Instantaneous Protection Pick-Up Adjustment Type li	Adjustable 9 settings
[li] Instantaneous Protection Pick-Up Adjustment Range	2...15 x In Off
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	Without
Local Signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error

Environment

Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	8.0 cm
Package 1 Length	21.5 cm
Package 1 Weight	318.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓

Mercury Free

✓

Rohs Exemption Information

Yes

✓

Pvc Free

Sertifikasi & Standar

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)