

Lembar data produk

Spesifikasi



Pieno - 16AX 250V 3 gang 1 way switch with fluorescent locator, white

E8233L1F_WE_G3

Main

Range	Pieno
Product Or Component Type	Switch
Device Application	Control
Switch Application	Switch
Load Type	Resistive Fluorescent
Cover Frame Colour Tint	White

Complementary

Device Mounting	Surface Flush
Wiring Device Mounting	Surface Flush
Switch Function	1-way
Rated Current	16 AX at 250 V AC 50 Hz
Local Signalling	Fluorescent (white)
Number Of Gangs	3 gangs
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	2 x 1.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s)
Embedding Depth	23 mm
Width	87 mm
Height	87 mm
Depth	23 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	SS 227-1 IEC 60669-1 MS IEC 60669-1 GB 16915.1 BS EN 60669-1

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	105.373 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	632.238 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	6322.38 g

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations