


Lembar data produk

Spesifikasi



Tap off unit, Canalis KS, for switch disconnecter FuPacT ISFT, 400A, 3L+PEN, with switch disconnecter, IP55, RAL9001

KSA40HD502

Main

Range Of Product	Canalis
Range Compatibility	Canalis KS busbar trunking
Product Or Component Type	Tap-off unit
Busbar Trunking Compatibility	Canalis KS busbar trunkingplug-in
[Ie] Rated Operational Current	400 A at 35 °C
Protection Type	fuse isolator: Efen fuse, size 2 conforming to DIN
Provided Equipment	fuse to be ordered separately
Mounting Mode	Plug-in with fixed polarity
Tap-Off Unit Polarity	3L+N+PE
Colour	White (RAL 9001)

Complementary

Device Application	Medium power distribution
[Uimp] Rated Impulse Withstand Voltage	6.8 kV
Network Frequency	50/60 Hz
Electrical Connection	Cable clamp terminal - ISO63 240 mm² flexible Cable clamp terminal - ISO63 240 mm² rigid
Door/Cover Opening Side	Right
Tap-Off Unit Disconnection Mode	By opening the door
Standards	IEC 61439-1 IEC 61439-6
Body Material	Metal
Width	587 mm
Depth	120 mm
Depth (Door Open)	763 mm
Height	350 mm
Net Weight	9 kg

Environment

Earthing System	TT TN-S IT
Ip Degree Of Protection	IP55 conforming to IEC 60529

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Ik Degree Of Protection	IK08 conforming to IEC 62262
--------------------------------	------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.0 cm
Package 1 Width	34.8 cm
Package 1 Length	57.3 cm
Package 1 Weight	9.0 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations