


Lembar data produk

Spesifikasi



ELBOW 630 A MADE TO MEASURE NEUTRAL INT

KSA630DLE4A

⚠ Telah dihentikan pada: 7 Jul 2021

⚠ Dihentikan

Main

Range Of Product	Canalis
Product Name	KS
Device Short Name	KSA
Product Or Component Type	Elbow
Busbar Description	Standard on made to measure
Device Application	Change direction
Conductors Material	Aluminium
[Ie] Rated Operational Current	500 A at 35 °C
[Ue] Rated Operational Voltage	230...690 V
Network Frequency	50/60 Hz
Operating Angle	90 °
Direction Change Type	direction 1: flat to upward -

Complementary

Width	147 mm
Depth	119 mm
Height	290...785 mm
Net Weight	4 kg
Mounting Location	On trunking
Mounting Position	Any position
Electrical Connection	Lubricated sliding contact
Mounting Mode	By screws
Standards	IEC 61439-6 IEC 61439-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12 cm
Package 1 Width	86.6 cm
Package 1 Length	86.6 cm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 1 Weight	19 kg
------------------	-------

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Product	

Sertifikasi & Standar

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins