


Lembar data produk

Spesifikasi



ZED 630 A MADE TO MEASURE

KSA630DZE4CF

⚠ Telah dihentikan pada: 7 Jul 2021

⚠ Dihentikan

Main

Range Of Product	Canalis
Product Name	KS
Product Or Component Type	Zed elbow
Busbar Description	Fire barrier
Device Application	Change direction
[Ie] Rated Operational Current	630 A at 35 °C
Ip Degree Of Protection	IP55 conforming to IEC 60529
[Ue] Rated Operational Voltage	230...690 V
Network Frequency	50/60 Hz
Operating Angle	90 °
Direction Change Type	direction 1: edgewise to upward - neutral to up direction 1: edgewise to left - neutral to up
Colour	White (RAL 9001)
Dimension Type	Made to measure
Length	290...785 mm for side A 250...745 mm for side C

Complementary

Width	111 mm
Depth	139 mm
Net Weight	18 kg
Electrical Connection	Lubricated sliding contact
Mounting Mode	By screws
Standards	IEC 61439-1 IEC 61439-6

Environment

Ik Degree Of Protection	IK08 conforming to IEC 62262
-------------------------	------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 1 Height	12 cm
Package 1 Width	96.7 cm
Package 1 Length	157 cm
Package 1 Weight	16 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Product	

Sertifikasi & Standar

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins