


Lembar data produk

Spesifikasi



Empty tap off unit, Canalis KS,
with isolator, polarity 3L+PEN,
160A, IP55, RAL9001

KSB160SV5

Main

Range Of Product	Canalis
Product Name	KS
Product Or Component Type	Empty tap-off unit
Product Compatibility	KS
[Ie] Rated Operational Current	160 A at 35 °C
Tap-Off Unit Polarity	3L+PEN

Complementary

Device Application	Low power distribution
[Ue] Rated Operational Voltage	230...690 V depending on protective device
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ui] Rated Insulation Voltage	690 V depending on protective device
Network Frequency	50/60 Hz
Tap-Off Unit Disconnection Mode	By drawing out
Tap-Off Unit Connector Type	With fixed polarity
Door Opening Size	630.5 mm
Door Opening Side	Right
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Standards	IEC 60439-2 IEC 61439-6
Body Material	Metal
Colour	White (RAL 9001)
Width	482 mm
Depth	207 mm
Height	332 mm
Net Weight	8 kg

Environment

Earthing System	TN-C - busbar trunking TN-C - tap-off unit
-----------------	---

Packing Units

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	29.0 cm
Package 1 Width	34.0 cm
Package 1 Length	60.5 cm
Package 1 Weight	8.38 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	8
Package 2 Height	73.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	77.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓ Reach Free Of Svhc	
✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations