

Lembar data produk

Spesifikasi



Enerlin'X IFE, Ethernet interface for circuit breakers

LV434001

Main

Range Of Product	ComPact NSX100...250 ComPact NSX400...630 ComPact NS630b...1600 ComPact NS1600b...3200
Device Short Name	IFE
Product Or Component Type	Interface module
Range Compatibility	Masterpact MasterPact MTZ Masterpact MasterPact NT Masterpact MasterPact NW ComPact ComPact NSX ComPact ComPact NS630b...1600 ComPact ComPact NS1600b...3200 PowerPact PowerPact J PowerPact PowerPact L PowerPact PowerPact H PowerPact PowerPact P PowerPact PowerPact R

Complementary

Communication Network Type	Ethernet, Modbus TCP/IP, HTTP, FTP, SMTP, NTP, SNMP10/100 Mbit/s on 2-port RJ45 Universal Logic Plug on 2-port RJ45
Web Server	Embedded HTTP server
Mounting Mode	By clips
Mounting Support	35 mm DIN rail
Control Type	By software
[Us] Rated Supply Voltage	24 V DC - 20...10 %
Maximum Supply Current	3 A
Current Consumption	120 mA
Connections - Terminals	RJ45 connector
Product Certifications	GOST cULus FCC CE
Standards	UL 60950 UL 508 IEC 60947-6-2 IEC 60950
Height	105 mm
Width	72 mm
Depth	71 mm
Net Weight	182.5 g

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Accessory / Separate Part Category	Spare part for Compact NS630b...1600 Spare part for Compact NS1600b...3200
------------------------------------	---

Environment

Ip Degree Of Protection	Connectors: IP2X Other parts: IP3x Front panel: IP4X
Relative Humidity	5...85 %
Ambient Air Temperature For Storage	-40...85 °C
Ambient Air Temperature For Operation	-20...70 °C
Pollution Degree	3
Flame Retardance	V0 conforming to UL 94 V0 conforming to IEC 60947-1 V0 conforming to IEC 60695-2-11
Shock Resistance	1000 m/s²
Vibration Frequency	5...8.4 Hz

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	7.2 cm
Package 1 Length	10.5 cm
Package 1 Weight	188.0 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	192
Package 2 Height	60.0 cm
Package 2 Width	80.0 cm
Package 2 Length	70.0 cm
Package 2 Weight	61.786 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	24
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	6.723 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	
 Halogen Free Plastic Parts Product	

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information