


Lembar data produk

Spesifikasi



TeSys F - contactor coil - LX1FL - 220...240 V AC 40...400 Hz

LX1FL220

⚠ Akan dihentikan pada: 31 Des 2028

⚠ Akan dihentikan

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1FL
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F630 LC1F1250
Control Circuit Type	AC at 40...400 Hz
[Uc] Control Circuit Voltage	220...240 V AC 40...400 Hz
Inductance Of Closed Circuit	3.35 H
Average Resistance	25.5 Ohm inrush at 20 °C 730 Ohm holding at 20 °C
Operating Time	100...200 ms opening 40...80 ms closing
Mechanical Durability	5 Mcycles
Maximum Operating Rate	1200 cyc/h 55 °C

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc 40...400 Hz (at 55 °C) Drop-out: 0.25...0.5 Uc 40...400 Hz (at 55 °C)
Inrush Power In Va	1650 VA 40...400 Hz cos phi 0.9 (at 20 °C)
Hold-In Power Consumption In Va	22 VA 40...400 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	20 W at 40...400 Hz

Environment

Ambient Air Temperature For Operation	-5...55 °C
Net Weight	1.5 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.000 cm
Package 1 Width	11.500 cm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 1 Length	23.000 cm
Package 1 Weight	1.410 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.027 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	48
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	83.036 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration