


Lembar data produk

Spesifikasi



current transformer tropicalised
1000 5 double output for bars
32x65

METSECT5DA100

Main

Range	PowerLogic
Product Name	CT
Product Or Component Type	Current transformer
Secondary Current	5 A
Accuracy Class	Class 0.5 at 15 VA Class 1 at 20 VA
[In] Rated Current	1000 A

Complementary

Current Transformer Type	Tropicalised for busbar
Current Transformer Ratio	1000/5
[Ith] Conventional Free Air Thermal Current	60 kA
Dynamic Withstand Current	2.5 Ith
Maximum Safety Factor	5
[Ue] Rated Operational Voltage	< 720 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	3 kV
Mounting Mode	Insulated locking screw
Mounting Support	Busbar
Width	Outside: 90 mm Inner: 65 mm
Height	Outside: 94 mm Inner: 32 mm
Depth	Frame : 40 mm Total : 87 mm
Net Weight	0.606 kg
[Uimp] Rated Impulse Withstand Voltage	3 kV
Electrical Insulation Class	Class B
Opening Of Bars	65 x 32
Sealing	With

Environment

Standards	VDE 0414 IEC 61869-2
-----------	-------------------------

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Product Certifications	CE EAC
Ip Degree Of Protection	IP20
Relative Humidity	0...95 %
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.3 cm
Package 1 Width	9.5 cm
Package 1 Length	10.1 cm
Package 1 Weight	564.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.143 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



RoHS/REACH

Kinerja kesejahteraan



Mercury Free



Rohs Exemption Information

Yes

Sertifikasi & Standar

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Weeee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins