

Lembar data produk

Spesifikasi



outlet grille plast cut out
125x125mm ext dim 137x117mm
IP54

NSYCAG125LPF

Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	ClimaSys ClimaSys CV fan
Product Or Component Type	Outlet grille
Accessory / Separate Part Category	Thermal management accessory
Accessory / Separate Part Destination	ClimaSys ventilation system
Fixing Mode	Clipped By screws
Device Composition	1 support frame 1 external part 1 G2 M1 synthetic standard filter

Complementary

Material	Injected thermoplastic (ASA PC)
Colour	External part: grey (RAL 7035)
Cut-Out Dimensions	125 x 125 mm
Height	External: 170 mm
Width	External: 150 mm
Depth	15 mm external:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	15.5 cm
Package 1 Length	18 cm
Package 1 Weight	220 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	56
Package 2 Height	38.5 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	13 kg

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Unit Type Of Package 3	P12
Number Of Units In Package 3	448
Package 3 Height	91 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	119 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations