

Lembar data produk

Spesifikasi



One double-profile mounting rail
35 x 15 2m for all enclosures
supply: 20



NSYDPR200T

Main

Anwendung	Multi-purpose
Range	Spacial
Product Or Component Type	Rail
Accessory / Separate Part Category	Mounting accessory
Type Of Rail	Double-profile DIN
Enclosure Nominal Dimensions	-
Range Compatibility	Spacial Thalassa
Device Composition	1 rail
Quantity Per Set	Set of 20

Complementary

Material	Galvanised steel
Surface Finish	Perforated
Fixing Mode	By fixing element - structure of enclosure location
Adjustment	Pitch 25 mm Continuous adjustment
Length	2000 mm
Height	Nominal: 15 mm
Width	Nominal: 35 mm
Thickness	1 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	8.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	948.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	8.0 cm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 2 Width	8.0 cm
Package 2 Length	200.5 cm
Package 2 Weight	21.686 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	720
Package 3 Height	80.0 cm
Package 3 Width	210.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	812.0 kg

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations